


TECHNICAL INFORMATION _ CAT. N. YL## FTCl 0000 A1900

FLOW THROUGH 180 VALVE 19 TANG. ON PIPE



Clean and Aseptic Valves of CAD Product Line have simple and safe design, with their full drainability, without asymptotic seal and dead leg, are offering fast cleanability and sterilization practices. They are designed to fulfil stringent demands of CIP-SIP and Production Cycles on Aseptic Processing.

YL## - FTCl - Tangential Flow Through on Pipe Valves for SAFE areas designed to feed or take off fluids or gases from the process piping with Zero dead leg. Valve inlet is tangential on pipe allowing full drainability of the pipeline on the horizontal valve assembly. Body shape and their internal design offer a very reliable component for Aseptic Processing Application. Standard version are short butt weld ends but, on demand, may be delivered for orbital welding or with Tri-Clamp connections.

CODE	A	B mm (inch)	C mm (inch)	D mm (inch)	E mm (inch)	F mm (inch)	G mm (inch)	TUBE 1* mm (inch)	TUBE 2* mm (inch)
YL25-FTCl-0000-A1900	M50x1	36,00 (1,42)	21,00 (0,83)	5,00 (0,20)	8,00 (0,32)	66,00 (2,60)	30,00 (1,18)	19,05x1,65 (0,75x0,065)	25,40x1,65 (1,00x0,065)
YL38-FTCl-0000-A1900	M50x1	42,50 (1,67)	27,50 (1,09)	5,00 (0,20)	8,00 (0,32)	66,00 (2,60)	25,00 (0,98)	19,05x1,65 (0,75x0,065)	38,10x1,65 (1,50x0,065)
YL50-FTCl-0000-A1900	M50x1	49,00 (1,93)	34,00 (1,34)	5,00 (0,20)	8,00 (0,32)	66,00 (2,60)	31,50 (1,24)	19,05x1,65 (0,75x0,065)	50,80x1,65 (2,00x0,065)
YL63-FTCl-0000-A1900	M50x1	60,00 (2,36)	40,00 (1,58)	5,00 (0,20)	8,00 (0,32)	66,00 (2,60)	38,00 (1,50)	19,05x1,65 (0,75x0,065)	63,50x1,65 (2,50x0,065)
YL76-FTCl-0000-A1900	M50x1	72,50 (2,85)	47,00 (1,85)	5,00 (0,20)	8,00 (0,32)	66,00 (2,60)	44,00 (1,73)	19,05x1,65 (0,75x0,065)	76,20x1,65 (3,00x0,065)

(*) US Tube ASTM® A269/270 – ASME BPE

SPECIFICATION:

CAD SIZE	A19						
-----------------	-----	--	--	--	--	--	--

NET VOLUME⁽¹⁾	ml	10,23					
---------------------------------	----	-------	--	--	--	--	--

⁽¹⁾ Internal valve cavity only, with diaphragm on site

MATERIAL	1,4435-BN2 - Low Ferrite - Low Sulphur						
-----------------	--	--	--	--	--	--	--

Design Temperature: -80 to 200 °C (-112 to 392 °F)

Application Areas: SAFE

Design Pressure, Valve Body: -1 to 10 bar (-14.5 to 145 psi)

Note: The applied actuator and diaphragm may have different design temperature and/or pressure limits. The weakest component determines the maximum design temperature and pressure limits, when they are assembled.

Surface Roughness: Internal surface (manually polished) $Ra \leq 0.3\mu m$ (16 μin)
External surface $Ra \leq 0.5\mu m$ (20 μin)

Surface Treatment: Available also on EP version - Elettropolishing after manual polished

Labeling: Each valve body is labeled for full LOT traceability

Packaging: Valve body is sealed in plastic bags and packaged in a closed box with Operating and Maintenance bulletin, Certificate of Conformity and Materials Certification 3.1

Quality Control: Quality Assurance System guarantees the control and traceability of the product.

Rules Compliances: CAD valve are on going to be classified for PED Directive 97/23/EC and fulfill ASME BPE Standards

Standard design: Shut Off bodies are available also to 180°, tangential outlet Left or Right

Options: For non-standard CAD Valve body Options, please contact us for further information.

Orders and Information: For additional information or to place a order call your nearest Distributor or visit www.rattiinox.com

Horizontal Assembly

